

## Display Examples

Press the Start button to see the following information display with each press of the start button:



**1. REC - 8.6C**  
shows Recording and current temperature



**2. RUN - 59 D**  
shows elapsed time in days



**3. MKT - 9.1C**  
shows mean kinetic temperature (available on silver model only)



**4. HI - 15.2C**  
shows alarm has occurred and high temperature (available on silver model only)



**5. LOW - 8.2C**  
shows alarm has occurred and low temperature



**6. HI HR - 0.3**  
shows alarm time hours over high threshold



**7. LOW HR - 1.1**  
shows alarm time hours over low threshold



**8. 14.9C**  
Push to return to current temperature